

FE-14126-R47



Fiber and power cable connection enclosure. Manages one 4-core or 8-core power trunk 12 AWG up to 6 AWG, one 24 fiber trunk cable and up to 7 hybrid tails. Internal trunk grounding. IP67

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Outdoor junction box

General Specifications

Color Gray

Mounting Pipe, 76.2 mm (3 in) OD | Wall

Dimensions

Height 304.8 mm | 12 in

Width 355.6 mm | 14 in

Depth 152.4 mm | 6 in

Material Specifications

Material Type High-impact polycarbonate, UV resistant

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space Indoor | Outdoor

Packaging and Weights

Included Mounting kit

Weight, net 1.996 kg | 4.4 lb

Regulatory Compliance/Certifications

FE-14126-R47

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

