



REVISIONS					
#	LR	DESCRIPTION	DATE	BY	APPD
A		RLSD PER NSD 06-006	26JAN06	LH	CC
B		REV-ECD-07-004743	01MAY07	LH	JG
C		REV-ECD-07-023001	16OCT07	LDS	JG
D		REV PER BNS_CD_BRAND	21JAN17	GG	DC



- ONE CABLE PACKAGED IN A POLY BAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS CAT6.
- DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.

30.48	100	30632.4 (1206.00)	9-1499841-9
.1500	.5	203.2 (8.00)	9-1499841-8
27.43	90	27584.4 (1086.00)	9-1499841-0
24.38	80	24536.4 (966.00)	8-1499841-0
22.86	75	23012.4 (906.00)	7-1499841-5
21.34	70	21488.4 (846.00)	7-1499841-0
18.29	60	18440.4 (726.00)	6-1499841-0
15.24	50	15392.4 (606.00)	5-1499841-0
13.72	45	13868.4 (546.00)	4-1499841-5
12.19	40	12344.4 (486.00)	4-1499841-0
10.68	35	10769.6 (424.00)	3-1499841-5
9.15	30	9296.4 (366.00)	3-1499841-0
7.62	25	7721.6 (304.00)	2-1499841-5
6.71	22	6807.2 (268.00)	2-1499841-2
6.1	20	6197.6 (244.00)	2-1499841-0
5.49	18	5588.0 (220.00)	1-1499841-8
4.88	16	4978.4 (196.00)	1-1499841-6
4.57	15	4724.4 (184.00)	1-1499841-5
4.27	14	4368.8 (172.00)	1-1499841-4
3.96	13	4064.0 (160.00)	1-1499841-3
3.66	12	3759.2 (148.00)	1-1499841-2
3.05	10	3149.6 (124.00)	1-1499841-0
2.74	9	2794.0 (110.00)	1499841-9
2.44	8	2489.2 (98.00)	1499841-8
2.14	7	2184.4 (86.00)	1499841-7
1.83	6	1879.6 (74.00)	1499841-6
1.53	5	1574.8 (62.00)	1499841-5
1.22	4	1270.0 (50.00)	1499841-4
0.92	3	965.2 (38.00)	1499841-3
0.61	2	660.4 (26.00)	1499841-2
0.30	1	355.6 (14.00)	1499841-1
METERS, REF		FEET, REF	PART NO



WIRING DIAGRAM
568B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRW T. HALL 12DEC2009	
DIMENSIONS: mm [INCHES]		CHK C. CASH 26JAN2006	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPD C. CASH 26JAN2006	
0 PLC ± -		PRODUCT SPEC	
2 PLC ± -		APPLICATION SPEC	
3 PLC ± -		114-13035	
4 PLC ± -		WEIGHT	
ANGLES ± -		CUSTOMER DRAWING	
FINISH		SCALE NTS	
MATERIAL		SIZE A2	
- 3		CAGE CODE 1499841	
		DRAWING NO	
		RESTRICTED TO	
		D	