



FACT® MPO Module, right sided, LC/APC at front side, 2x12 fiber MPO at rear side, singlemode, wiring method B Enhanced

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	FACT®
Product Series	FACT

General Specifications

Functionality	Breakout
Application	For Use with FACT NG4 Universal Chassis
Body Style	Right orientation
Color, boot	Black
Color, housing	Black
Color, rear	Green
Interface, front	LC/APC
Interface Feature, front	Simplex
Interface Color, front	Green
Interface, rear	MPO
Interface Feature, rear	Female Key up/up Unpinned
Interface Color, rear	Green
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	24
Total Ports, quantity, front	24
Total Ports, quantity, rear	2

760244561 | FACT-MMDRME-B

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	122.68 mm 4.83 in

Optical Specifications

Fiber Mode	Singlemode
Insertion Loss, maximum	0.75 dB
Insertion Loss, typical	0.6 dB
Return Loss, minimum	62 dB

Environmental Specifications

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 85%, non-condensing

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

