

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© 2016 CommScope, INC. Confidential


NOTED: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purposes authorized in writing by COMMSCOPE, INC.

REVISIONS

P	LTN	DESCRIPTION	DATE	DRW	APPD
H		40053026CMO	25OCT2017	RL	GW

1 → 8
(P1)1 → 8
(P2)

- ONE CABLE PACKAGED IN A POLY BAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: SHIELDED 26 AWG, 4 TWISTED PAIRS, 7/34 STRANDED CONDUCTORS, 100 OHMS CAT6A.
- DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.

WIRING DIAGRAM
568B

30.48	100	30632.4 (1206.00)	9-1933883-9	8.53	28	8686.8 (342.00)	2-1933883-8
0.15	0.5	203.2 (8.00)	9-1933883-8	7.92	26	8077.2 (318.00)	2-1933883-6
28.96	95	29108.4 (1146.00)	9-1933883-5	7.32	24	7416.8 (292.00)	2-1933883-4
27.43	90	27584.4 (1086.00)	9-1933883-0	6.71	22	6807.2 (268.00)	2-1933883-2
25.91	85	26060.4 (1026.00)	8-1933883-5	6.1	20	6197.6 (244.00)	2-1933883-0
24.38	80	24536.4 (966.00)	8-1933883-0	5.49	18	5588.0 (220.00)	1-1933883-8
22.86	75	23012.4 (906.00)	7-1933883-5	4.88	16	4978.4 (196.00)	1-1933883-6
21.34	70	21488.4 (846.00)	7-1933883-0	4.57	15	4673.6 (184.00)	1-1933883-5
19.81	65	19964.4 (786.00)	6-1933883-5	4.27	14	4368.8 (172.00)	1-1933883-4
18.29	60	18440.4 (726.00)	6-1933883-0	3.66	12	3759.2 (148.00)	1-1933883-2
16.76	55	16916.4 (666.00)	5-1933883-5	3.05	10	3149.6 (124.00)	1-1933883-0
15.24	50	15392.4 (606.00)	5-1933883-0	2.74	9	2794.0 (110.00)	1933883-9
13.72	45	13868.4 (546.00)	4-1933883-5	2.44	8	2489.2 (98.00)	1933883-8
12.20	40	12344.4 (486.00)	4-1933883-0	2.14	7	2184.4 (86.00)	1933883-7
11.58	38	11734.8 (462.00)	3-1933883-8	1.83	6	1879.6 (74.00)	1933883-6
10.97	36	11125.2 (438.00)	3-1933883-6	1.53	5	1574.8 (62.00)	1933883-5
10.36	34	10515.6 (414.00)	3-1933883-4	1.22	4	1270.0 (50.00)	1933883-4
9.75	32	9906.0 (390.00)	3-1933883-2	0.92	3	965.2 (38.00)	1933883-3
9.14	30	9296.4 (366.00)	3-1933883-0	0.61	2	660.4 (26.00)	1933883-2
				0.30	1	355.6 (14.00)	1933883-1
METERS, REF	FEET, REF	DIM A	PART NO	METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DATE 20NOV2016 R.L.I.		DATE 20NOV2016 F.ZHANG		NAME W.FAN		CABLE ASSY, MOD PLUG, 8 POSN, SHIELDED, GREEN, CAT 6A	
0 PLC ± -		2		PRODUCT SPEC		APPLICATION SPEC		SIZE A2		CAGE CODE 00779	
1 PLC ± -		2		WEIGHT		SCALE		SHEET		1 of 1	
2 PLC ± -		2		CUSTOMER DRAWING		SCALE		SHEET		1 of 1	
3 PLC ± -		2									
4 PLC ± -		2									
ANGLES		FINISH									
MATERIAL		FINISH									