

# RCP-4ZBPUZ16045B

---



RapidFiber® Termination Panel, 288-Position 4RU, singlemode, LC/APC to LC/APC breakouts, 160m cable with 45 inch breakout length and 1.2 MM Breakout Jacketing

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel, with rapid cable
<b>Product Brand</b>	RapidFiber®
<b>Product Series</b>	RCP

## General Specifications

<b>Functionality</b>	Patching
<b>Body Style</b>	Symmetrical
<b>Cable Exit Location</b>	Rear, left side
<b>Cable Stub Type</b>	IFC, stranded
<b>Color</b>	Putty white
<b>Door Type, front</b>	Hinged   Slide latch   Transparent
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LC/APC
<b>Interface, rear</b>	LC/APC
<b>Patch Cord Entry Location</b>	Front, left side   Front, right side
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Sliding
<b>Total Fibers, quantity</b>	288
<b>Total Ports, quantity</b>	288
<b>Transmission Standards</b>	IEC 60794-2   ISO/IEC 11801   TIA/EIA-568-B.3


## Dimensions

<b>Height</b>	177.8 mm   7 in
---------------	-----------------

# RCP-4ZBPUZ16045B

<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	381 mm   15 in
<b>Breakout Length</b>	45 in

## Ordering Tree



ONLY FOR MULTIMODE VERSION.<sup>1</sup>  
 ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE<sup>2</sup>  
 RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.<sup>3</sup>  
 ONLY AVAILABLE IN LC288 4RU<sup>4</sup>

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.652.D   G.657.A2/B2

# RCP-4ZBPUZ16045B

---

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +55 °C (+23 °F to +131 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–85%, non-condensing
<b>Qualification Standards</b>	NEBS Level 3   Telcordia GR-1435   Telcordia GR-326   Telcordia GR-409   UL 1863

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Included Products

760245201 P-024-MP-8V-F30YL	–	Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
--------------------------------	---	--