

# FPM-0M/O-M003M

---

Fiber Optic Pigtail, OS2, LC/APC-stub, 12F soft wall 900  $\mu$ m buffered fiber, 3 m, yellow, 12" breakout

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber pigtail, multi-fiber
<b>Product Series</b>	FPM

## General Specifications

<b>Connector A, quantity</b>	12
<b>Color, boot A</b>	Green
<b>Color, connector A</b>	Green
<b>Construction Type</b>	Stranded
<b>Interface, Connector A</b>	LC/APC
<b>Jacket Color</b>	Yellow
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Cord Length</b>	3 m   9.843 ft
--------------------	----------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum, connector A</b>	0.35 dB
<b>Return Loss, minimum, connector A</b>	65 dB

## Environmental Specifications

<b>Environmental Space</b>	Plenum
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

# FPM-0M/0-M003M

---

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

