

IFC-7/OVP061-PPV

Fiber Optic Intra Facility Fiber Cable, OS2, SC/UPC to Stub, yellow, 61 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	IFC

General Specifications

Connector A, quantity	72
Color, boot A	Blue
Color, connector A	Blue
Connector B, quantity	0
Interface, Connector A	SC/UPC
Interface, Connector B	Unterminated
Jacket Color	Yellow
Total Fibers, quantity	72

Dimensions

Cord Length	61 m 200.131 ft
--------------------	-------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.2 dB
Return Loss, minimum, connector A	55 dB

Environmental Specifications

Environmental Space	Riser
----------------------------	-------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

IFC-7/OVP061-PPV

Agency**Classification**

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

