# IFC-7/7VP016-PPV

### Fiber Optic Intra Facility Fiber Cable, OS2, SC/UPC to SC/UPC, yellow, 16 m

### Product Classification

Regional Availability	Latin America   North America
Product Type	Fiber distribution cable assembly
Product Series	IFC
General Specifications	
Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	72
Connector B, quantity	72
Interface, Connector A	SC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	72
Dimensions	
Cord Length	16 m   52.493 ft
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.2 dB
Insertion Loss, maximum, connector B	0.2 dB
Return Loss, minimum, connector A	57 dB
Return Loss, minimum, connector B	57 dB

#### **Environmental Specifications**

**Environmental Space** 

Riser

Page 1 of 2

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 4, 2021



## IFC-7/7VP016-PPV

### Packaging and Weights

Packaging quantity

1

### Regulatory Compliance/Certifications

#### Agency

CHINA-ROHS

Classification

**REACH-SVHC** 

ROHS



Above maximum concentration value Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant/Exempted

Page 2 of 2

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 4, 2021

