


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
C		ECN 8000019229 - REBRANDING	20DEC2016	TZ JS



NOTES:

1. INSERTION LOSS $\leq 0,3$ dB, MEASURED AGAINST REF. CONNECTOR
2. RETURN LOSS ≥ 45 dB, IN MATED CONDITION
3. TUNED CONNECTOR
4. INFO ON BAG LABEL:
 - PART NUMBER
 - PO NUMBER
 - MANUFACTURING DATE
 - INSERTION LOSS AND RETURN LOSS AT 1310nm
5. CABLE INFO:
 - CORE DIA: 9/125 μ m
 - OUTER DIA: 0,9 mm
 - BUFFER COLOUR: WHITE
 - BUFFER MATERIAL: LSZH
 - STRIPPABILITY: SEMI TIGHT

STANDARD LENGTHS ACCORDING TO
CUSTOMER DRAWING 1206850

PART NUMBER	"L" (meter)
X-5233582-Y	XY,0

Qty	Part Number	Description	Item
1	-	BAG LABEL \triangle 4	-
1	-	FOAC DUSTCAP SC BLACK NO STRAP	8
1	-	FOAC CONN HOUSING SC BLUE	7
1	-	FOAC CONN PLUG BODY SC GRAY	6
1	-	FOAC FERRULE ASSY SC/PC 125/1,1	5
1	-	FOAC SPRING COMPRESSION 2,4	4
1	-	FOAC INTERNAL BODY SC 2,4 KNURLED	3
1	-	BOOT BARE FIBRE RED	2
L	-	FOCAB 0,9 9/125S WHITE LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. MIDDELDORP 03 JAN 97	COMMSCOPE, INC.	
		CHK ARIE HENGELMOLEN 31 DEC 04		
		APVD ARIE HENGELMOLEN 31 DEC 04	NAME	
DIMENSIONS: mm		PRODUCT SPEC		SIZE A2
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		CAGE CODE -
0 PLC \pm -		WEIGHT -		DRAWING NO C=5233582
1 PLC \pm -		RESTRICTED TO		
2 PLC \pm -		SCALE 1:1		SHEET 1 of 1
3 PLC \pm -		REV C		
4 PLC \pm -				
ANGLES \pm -				
FINISH				
MATERIAL		CUSTOMER DRAWING		

5233582