

# 760248104 | ODF-SPLCAB-12



UMSC (Universal Mounted Splice Cabinet) with up to 3456 fiber splices capacity (Rollable ribbon cables), exit up, gray

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Universal Mounted Splice Cabinet
<b>Product Series</b>	ODF

## General Specifications

<b>Access</b>	Front
<b>Cable Entry Location</b>	Top
<b>Cable Exit Location</b>	Top
<b>Color</b>	Gray
<b>Growth Configuration</b>	Unloaded
<b>Mounting</b>	Back to Back   Rack, EIA 19 in   Rack, EIA 23 in   Wall
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity Note</b>	Up to 3456 Rollable ribbon splice
<b>Splicing Capacity, maximum</b>	3456

## Dimensions

<b>Height</b>	1,074.2 mm   42.291 in
<b>Width</b>	430 mm   16.929 in
<b>Depth</b>	287.9 mm   11.335 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# 760248104 | ODF-SPLCAB-12

---

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

