

760248104 | ODF-SPLCAB-12



ODF-SPLCAB-12, up to 3456 fiber splices (Rollable ribbon cables), exit up, gray

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Universal Splice Cabinet
Product Brand	ODF
Product Series	ODF

General Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Color	Gray
Growth Configuration	Unloaded
Mounting	Back to Back Rack, EIA 19 in Rack, EIA 23 in Wall
Splice Trays Included, quantity	0
Splicing Capacity Note	Up to 3456 Rollable ribbon splice
Splicing Capacity, maximum	3456

Dimensions

Height	1074 mm 42.283 in
Width	465 mm 18.307 in
Depth	300 mm 11.811 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

