







LOC	DIST	REVISIONS				
HM	00	P	LTR	DESCRIPTION	DATE	APVD
			L1	SUPERSEDED; 40024507MCO	03SEP2015	GG SJ
			M	REV PER BNS_CD_BRAND	20JAN2017	GG DC



- 1 MATERIAL:
HOUSING—94V-0 RATED POLYCARBONATE,CLEAR.
TERMINAL—0.36 [.014] THICK PHOSPHOR
BRONZE PLATED WITH 0.178um [.000007]
GOLD IN LOCALIZED AREA OVER 0.762um [.000030]
PALLADIUM NICKEL IN LOCALIZED AREA,
OVER 2.54um [.000100] NICKEL UNDERPLATE
COVERING THE ENTIRE TERMINAL.
LOAD BAR — PBT POLYESTER, BLACK.
- 2 DIMENSIONS ARE MAXIMUM UNLESS
OTHERWISE SPECIFIED.
3. PLUG WILL ACCEPT A 24 AWG STRANDED
CONDUCTOR, PROVIDED THE INSULATED
CONDUCTOR DIAMETER IS LESS THAN OR
EQUAL TO 0.99 [.039]; WITH A MAXIMUM
CABLE JACKET DIAMETER OF 5.59 [.220],
MINIMUM 4.83 [.190].
- 4 TERMINATED DIMENSION 6.15[.242]
MAXIMUM.
- 5 500 ASSEMBLIES AND 500 LOAD
BARS PER PACKAGE.
- 6 100 ASSEMBLIES AND 100 LOAD
BARS PER PACKAGE.
9. UL RECOGNIZED: FILE NUMBER E81956

SUPERSEDED BY: 2843004
REFERENCE CATALOG SERIES MP-5EU-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. WOOTEN 5-31-94	COMMSCOPE, INC.			
DIMENSIONS: mm[INCHES]		CHK D. HUSSEY 7-13-94				
		APVD —	NAME MODULAR PLUG ASSEMBLY, 8 POSITION, ROUND CABLE, STRANDED WIRE			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1163				
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		APPLICATION SPEC 114-6053	SIZE A2	CAGE CODE	DRAWING NO C=558530	RESTRICTED TO —
MATERIAL - 1		WEIGHT —	CUSTOMER DRAWING		SCALE 4.1	SHEET 1 of 1
					REV M	