

TFBH17E/17E/100-3 | ION-B EU L 17E/17E VDC/100



ION®-B Series Extension Unit for AWS 1700 Band Applications

Product Classification

Product Type	Extension unit
Product Brand	ION®-B

General Specifications

Note	CrossBandCoupler included Jumper (1 dB loss maximum)
Power Type	High

Electrical Specifications

Impedance	50 ohm
License Band	AWS 1700
Voltage Range	-60 to -36 Vdc

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	2110 – 2180 MHz (AWS 1700)
---------------------------------	----------------------------