

# TFBH23/23-3 | ION-B EU L 23/23 VDC

---



## ION®-B Series Extension Unit for WCS2300 Band Applications

### Product Classification

<b>Product Type</b>	Extension unit
<b>Product Brand</b>	ION®-B

### General Specifications

<b>Note</b>	CrossBandCoupler included   Jumper (1 dB loss maximum)
<b>Power Type</b>	High

### Electrical Specifications

<b>Impedance</b>	50 ohm
<b>License Band</b>	WCS 2300
<b>Voltage Range</b>	-60 to -38 Vdc

### Electrical Specifications, Tx (Downlink)

<b>Operating Frequency Band</b>	2350 – 2360 MHz (WCS 2300)
---------------------------------	----------------------------