

TFBH25T/25T-1 | ION-B EU L 25T/25T VAC



ION®-B Series Extension Unit for TDD 2500 Band Applications

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Product Type	Extension unit
Product Brand	ION®-B

General Specifications

Communications Port Interface	QMA Female
Communications Port, quantity	8
Note	CrossBandCoupler included Jumper (1 dB loss maximum)
Power Class	High

Electrical Specifications

Impedance	50 ohm
License Band	TDD 2500
Voltage Range	100 to 240 Vac

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	2496 – 2690 MHz (TDD 2500)
---------------------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

TFBH25T/25T-1 | ION-B EU L 25T/25T VAC

ROHS Compliant

UK-ROHS Compliant

