

TFBH25T/25T-1 | ION-B EU L 25T/25T VAC



ION®-B Series Extension Unit for TDD 2500 Band Applications

Product Classification

Product Type	Extension unit
Product Brand	ION®-B

General Specifications

Communications Port Interface	QMA Female
Communications Port, quantity	8
Note	CrossBandCoupler included Jumper (1 dB loss maximum)
Power Type	High

Electrical Specifications

Impedance	50 ohm
License Band	TDD 2500
Voltage Range	+100 to +240 Vac

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	2496 – 2690 MHz (TDD 2500)
---------------------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

