


Connector Attachment


For Braided Cable CNT-400 & C2FP UHF Male, Solder Pin, Clamp-type Body: 400PUM

Bulletin 7559511 Revision A Page 1 of 2




Remove 7.5 mm (0.295") of Jacket only 7.5 mm (0.295")


Slide parts A, B, C onto the cable. Note: the direction of part C as shown.




Comb braid straight with a wire brush.




Install part D as shown without damaging the braid.




Fold braid around part D and comb braid as shown, the braid should be straight and equally spaced after comb.




Cut off the redundant braid as shown.




Remove 6.0 mm (0.236") of foam. Remove all foam/glue residue from the center conductor.




Chamfer the center conductor at a 45° angle.



Push parts E, F onto the cable center conductor.




Solder part F and cable center conductor 10 together. Inspect soldering point, solder should fill cup but not spill over.



The cable attachment must be straight and aligned with the hole of connector inner contact. Insert the cable attachment into connector body until stopped; the center conductor must be inserted into the hole of insulator. Tighten the connection to the torque value of 60-80 lb-in (6.8-9.0 Nm). Note: Do not turn connector body, turn cable attachment.

The V type part C are splitted into two pieces after part A installation.



502	表一 有毒有害物质或元素名称及含量标识格式					
	有毒有害物质或元素					
部件名称(Part Name)	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr6+)	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
连接器 (Connector)	Х	0	0	0	0	0

O:表示有毒有害物质在该部件所有的均质材料中的含量均在SJ/T 11363-2006规定的限量要求以下 . X:表示该有毒有害物质至少在该部件的某一均质材料中的含量超出SJ/T 11363-2006规定的限量要 求.

ANDREW an Amphenol company 2601 Telecom Parkway, Richardson, Texas, 75082, USA www.andrew.com

Technical Support

+1 888 297 6433, Option 3 (Toll Free US and Canada) awpnarsupport@andrew.com

Notice: ANDREW disclaims any liability or responsibility for the results of improper or unsafe installation, inspection, maintenance, or removal practices. Aviso: ANDREW no acepta ninguna obligación ni responsabilidad como resultado de prácticas incorrectas o peligrosas de instalación, inspección, mantenimiento o retiro. Avis: ANDREW décline toute responsabilité pour les conséquences de procédures d'installation, d'inspection, d'entretien ou de retrait incorrectes ou dangereuses. Hinweis: ANDREW lehnt jede Haftung oder Verantwortung für Schäden ab, die aufgrund unsachgemäßer Installation, Überprüfung, Wartung oder Demontage auftreten. Atenção: A ANDREW abdica do direito de toda responsabilidade pelos resultados de práticas inadequadas e sem segurança de instalação, inspeção, manutenção ou remoção. Avvertenza: ANDREW declina eventuali responsabilità derivanti dell'esecuzione di procedure di installazione, ispezione, manutenzione e smontaggio improprie o poco sicure. 注意: ANDREW 公司申明對於不恰當或不安全的安裝、檢驗、維修或拆卸操作所導致的后果不負任 何義務和責任