

760248150 | G2-SP-12LAG-RPT



G2 Splice Cassette, 12LC/APC with internal shutters, OS2, with ribbon pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with ribbon pigtail
Product Series	G2

General Specifications

Color, front	Green
Interface, front	LC/APC
Interface, rear	Ribbon pigtail
Polarity	Pairs, straight
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	26.416 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	165.354 mm 6.51 in

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.4 dB
Return Loss, minimum	60 dB

760248150 | G2-SP-12LAG-RPT

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL

Packaging and Weights

Included SMOUV holder | SMOUV splice protection

Packaging quantity 1

Weight, net 0.113 kg | 0.25 lb