

# NGFB-TB5SLUK

---



Next Generation Frame (NGF) Fiber Termination Block, LC/UPC, Adapter only, Left Block

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber patch block
<b>Product Series</b>	NGFB

## General Specifications

<b>Functionality</b>	Patching
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Left orientation
<b>Cable Exit Location</b>	Upward
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Door Type, front</b>	Compression latch   Hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LC/UPC
<b>Rack Type</b>	NGF
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	288

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

# NGFB-TB5SLUK

---

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 80%, non-condensing
<b>Qualification Standards</b>	Telcordia GR-449-CORE

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---