

# F1-HMHM-3-SGW-D



D-CLASS FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing boot , 3 ft

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ1-50A

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

## Dimensions

Length	0.91 m   2.986 ft
Nominal Size	1/4 in

## Logo Image

# F1-HMHM-3-SGW-D



## Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.152	23.02
1700–2200 MHz	1.152	23.02
2500–2700 MHz	1.152	23.02

## Jumper Assembly Sample Label

# F1-HMHM-3-SGW-D



## Environmental Specifications

<b>Immersion Test Method</b>	Meets IEC 60529:2001, IP68 in mated condition
<b>Weatherproofing Method</b>	HELIAX® SureGuard weatherproofing boot

## Packaging and Weights

<b>Included</b>	Weatherproofing boot
-----------------	----------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system