

G2 MPOptimate® Singlemode MPO-12 Distribution Module, 12SC APC to 1x12f MPO pinned , dust plugs

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	G2

General Specifications

Color, front	Green
Color, rear	Black
Interface, front	SC
Interface Feature, front	APC
Interface, rear	MPO Pinned
Interface Feature, rear	Key up/down
Polarity	Method A Pairs, straight
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	117.35 mm 4.62 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.92 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

