


FACT-MMDKEOLOUB-S



FACT® MPO Module, singlemode, Ultra Low Loss (ULL), LC/UPC-MPO 24 fiber, left exit (for MPO module)

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	FACT®
Product Series	FACT

General Specifications

Functionality	Breakout
Application	For use with FACT panels
Adapter Color	Aqua
Adapters, quantity, front	12
Body Style	Duplex Straight orientation
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Standard
Polarity	Pairs, straight
Total Ports, quantity, front	24

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in

FACT-MMDKEOLOB-S

Depth 122.68 mm | 4.83 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D and G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -5 °C to +40 °C (+23 °F to +104 °F)

Storage Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Relative Humidity Up to 85%, non-condensing

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

