

## LSA-Plus® Backmount Frame, 19 in, 18-way, 4 RU, recessed



### Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Copper patch panel
<b>Product Brand</b>	LSA-PLUS®
<b>Product Series</b>	Highband

### General Specifications

<b>Application</b>	For use with LSA-PLUS modules
<b>Color</b>	Silver
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	LSA-PLUS module
<b>Modules, quantity</b>	18
<b>Panel Mounting</b>	Flush
<b>Panel Style</b>	Straight
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	4

### Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Steel
----------------------	---

### Packaging and Weights

64271001-00 | 64271001-00

---

**Packaging quantity** 1  
**Packaging Type** Bag | Box

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

