

# 760248151 | G2-SP-24LAG-RPT



G2 Splice Cassette, 24LC/APC with internal shutters, OS2, with ribbon pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with ribbon pigtail
<b>Product Series</b>	G2

## General Specifications

<b>Color, front</b>	Green
<b>Interface, front</b>	LC/APC
<b>Interface, rear</b>	Ribbon pigtail
<b>Polarity</b>	Pairs, straight
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Height</b>	26.416 mm   1.04 in
<b>Width</b>	96.52 mm   3.8 in
<b>Depth</b>	165.354 mm   6.51 in

## Material Specifications

<b>Alignment Sleeve Material</b>	Zirconia
----------------------------------	----------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.4 dB
<b>Return Loss, minimum</b>	60 dB

# 760248151 | G2-SP-24LAG-RPT

---

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** UL

## Packaging and Weights

**Included** SMOUV holder | SMOUV splice protection

**Packaging quantity** 1

**Weight, net** 0.123 kg | 0.271 lb