


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
H	—		E1	REVISED PER EXO-11-005294	02APR11	RK	HMR
			F	ECN 8000017738 - REBRANDING	22NOV2016	LS	OV



LC CONN. SIDE MARK		LC CONN. SIDE MARK
A	→	B
B	→	A

NOTES:

- ATTENUATION ≤ 0.3 dB, MEASURED AGAINST REFERENCE CONNECTOR
 - RETURN LOSS ≥ 45 dB, IN MATED CONDITION
 - TUNED CONNECTORS
 - INFORMATION ON CABLE LABEL:
 - UNIQUE SERIAL NUMBER
 - COMMSCOPE PART NUMBER
 - PO NUMBER
 - ATTENUATION AND RETURN LOSS AT 1310 nm
 - BLANK LABEL
 - CABLE INFORMATION:
 - CORE DIAMETER: 9/125 μm
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: YELLOW
 - OUTER JACKET MATERIAL: LSZH
- FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY
- DELIVERED ON A REEL IN A BOX

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-6536501-Y	XY.0
8-6536501-1	200 -0/+10
8-6536501-2	100 -0/+3
8-6536501-3	125 -0/+6
8-6536501-6	0.25 -0/+0.05
9-6536501-0	0.5 -0/+0.1

2	BLANK LABEL	4
4	INFORMATION LABEL	3
2	LC DUPLEX CONNECTOR, SINGLE MODE, BLUE	2
L	FOCAB 1.8MZ 9/125, YELLOW LSZH	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
OWN: R. COOLEN 01AUG2007 CHK: A. HENGELMOLEN 10AUG2007 APVD: A. HENGELMOLEN 10AUG2007		NAME: COMMSCOPE, INC.
DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ - 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ - FINISH -		PRODUCT SPEC: APPLICATION SPEC: WEIGHT: - CUSTOMER DRAWING
SIZE: A2 CAGE CODE: - DRAWING NO: C-6536501		RESTRICTED TO: -
SCALE: NTS		SHEET: 1 OF 1 REV: F