


1

LOC	DIST	REVISIONS					
H	—	P	LTR	DESCRIPTION	DATE	OWN	APVD
		J		ECR-09-013985	07JUL2009	RC	AH
		K		ECN 8000017738 — REBRANDING	22NOV2016	LS	OV




LC CONN. SIDE MARK	LC CONN. SIDE MARK
A	B
B	A

NOTES:

- ATTENUATION ≤ 0.3 dB, MEASURED AT 1300 nm
ACC. TO I.E.C. 61300-3-4 METHOD B
- BLANK LABEL
- FILLED OUT TEST RESULT SHEET SUPPLIED
WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- CABLE INFORMATION:
 - CORE DIAMETER: 50/125 μ m
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: ORANGE
 - OUTER JACKET MATERIAL: LSZH
- FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY
- ADDITIONAL ATTENUATION FOR LONG LEADS
ACC. TO CUSTOMER DRAWING 1920435
- DELIVERED ON A REEL IN A BOX

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-6536502-Y	XY.0
8-6536502-1	100.0 -0/+5
8-6536502-2	300 -0/+15
9-6536502-0	0.5 -0/+0.1

2	BLANK LABEL	3
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ 50/125, ORANGE LSZH	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS:		OWN R. COOLEN 01AUG2007
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		CHK A. HENGELMOLEN 10AUG2007
mm		APVD A. HENGELMOLEN 10AUG2007
		NAME
MATERIAL		FORM50 LEAD 1.8MZ LC/PC - LC/PC DUPLEX
-		SIZE
-		CAGE CODE
-		DRAWING NO
-		RESTRICTED TO
-		A2
-		G=6536502
-		SCALE
-		NTS
-		SHEET
-		1 OF 1
-		REV K
CUSTOMER DRAWING		