


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
E		ECN8000019304 - REBRANDING	22DEC2016	CY JS



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 850nm ACC. TO I.E.C. 61300-3-4 INSERTION METHOD B WITH MODAL CONDITION ACCORDING TO: IS 14763-3, OFSTP-14, IEC 61280-4-1
- 2 RETURN LOSS ≥ 25 dB, MEASURED IN MATED CONDITION AGAINST REF. CONNECTOR AT 850nm
- 3 SUPPLIED WITH FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY AND A DAT LABEL



DAT LABEL INFO:

- UNIQUE SERIAL NUMBER
- COMMSCOPE PART NUMBER
- MANUFACTURING LOCATION

5 CABLE INFO:

- OM3 BIMM
- CORE DIA - 50/125 μ m
- OUTER DIA - 0,9 mm
- BUFFER COLOR - AQUA
- BUFFER MATERIAL - UV CURED ACRYLATE

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-6536555-Y	XY,0

Qty	Description	Item
1	FOAC DAT-85 LABEL	-
1	PROTECTIVE COVER, 2.5MM, BLACK	5
1	HSNG, SC SIMPLEX, BEIGE	4
1	S/A,CONN. SC ,MM 125 μ m	3
1	BOOT,BARE FIBER, BLACK	2
L	FOCAB 0.9S 50/125 OM3 AQUA	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 01 SEP 05	COMMSCOPE, INC.	
DIMENSIONS: mm		CHK DIWAKAR BELAVADI 16 DEC 05		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DIWAKAR BELAVADI 16 DEC 05	NAME -	
0 PLC \pm -		PRODUCT SPEC	FOMM50 PIGTAIL 0,9S OM3 SC	
1 PLC \pm -		APPLICATION SPEC	SIZE A2	CAGE CODE -
2 PLC \pm -		WEIGHT -	DRAWING NO C=6536555	RESTRICTED TO -
3 PLC \pm -		MATERIAL -	SCALE NTS	SHEET 1 of 1
4 PLC \pm -		FINISH -	CUSTOMER DRAWING	REV E
ANGLES \pm -				

6536555

A