


LOC	DIST	REVISIONS					
H	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			J	ECN 8000017776—REBRANDING	15-DEC-16	SC	JV



STANDARD LENGTHS ACCORDING TO PRODUCT DRAWING 1206850	
PART NUMBER	"L" (meter)
X-6536969-Y	XY.0
8-6536969-1	1.5 -0/+0.1
8-6536969-2	2.5 -0/+0.1
8-6536969-3	3.5 -0/+0.1
8-6536969-4	100 -0/+3.0
8-6536969-5	150 -0/+3.0
8-6536969-5	90 -0/+3.0
8-6536969-7	120 -0/+3.0
9-6536969-0	0.5 -0/+0.1
9-6536969-1	0.75 -0/+0.1
9-6536969-2	0.2 -0/+0.03
9-6536969-9	85 -0/+3.0

LC CLIP SIDE MARK		LC CLIP SIDE MARK
A		B
B		A

NOTES:

- | | | |
|---|--|--|
| 1 | ATTENUATION | 0.3 dB, MEASURED AT 850 nm I.E.C. 61300-3-4 METHOD B |
| 2 | RETURN LOSS | 30 dB, IN MATED CONDITION |
| 3 | FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY | |
| 4 | BLANK LABEL | |
| 5 | CABLE INFORMATION: | |
| | - CORE DIAMETER: | 50/125 μ m |
| | - OUTER JACKET DIAMETER: | 1.8x3.6 mm |
| | - OUTER JACKET COLOUR: | AQUA |
| | - OUTER JACKET MATERIAL: | LSZH |

6 FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY

 LABEL INFORMATION:

PART NUMBER
SERIAL NUMBER
ORDER NUMBER
CABLE LENGTH

2	LABEL	3
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
1	FOCAC 1.8MZ OM3 50/125, AQUA LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 01AUG2007 CHK A. HENGELMOLEN 01AUG2007 APD A. HENGELMOLEN 01AUG2007	COMMScope, Inc. FOMM50 OM3 LEAD 1.8MZ LC DUPLEX - LC DUPLEX	
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ± -	NAME PRODUCT SPEC - APPLICATION SPEC -	SIZE A2	GAGE CODE -
MATERIAL -	FINISH -	WEIGHT -	DRAWING NO C=6536969	
CUSTOMER DRAWING			RESTRICTED TO -	
			SCALE	NTS
			SHEET	1 of 1
			REV	