






ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	MTC79021414.01	14' SIDE CHANNEL	2	159.09 LBS
2	MTC79020808.01	8' CENTER CHANNEL	5	86.28 LBS
3	MTC7902.03	CHANNEL ADAPTER ANGLE	10	7.07 LBS
4	MTC79020808.04	8' GRATING SECTION BRACKET	1	42.93 LBS
5	MTC79020407.03	24" X 84" BAR GRATING	8	99.90 LBS
6	GB-05205	5/8" X 2" GALV BOLT KIT	42	0.31 LBS
7	GWF-05	5/8" GALV FLAT WASHER	84	0.01 LBS
8	GCM03	GRATING CLIP	48	




DETAIL A

REV.		ZONE	DESCRIPTION	BY	DATE
A			INITIAL RELEASE	MSM	02/18/11



- NOTES:
- ALL METRIC DIMENSIONS ARE IN BRACKETS.
 - UP TO 5% ADDITIONAL HARDWARE INCLUDED.
 - BAR GRATING ALIGNED ACROSS CENTER CHANNELS.

These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific purpose authorized in writing by Andrew Corporation. ALL DIMENSIONS ARE IN INCHES U.S.S. TOLERANCES UNLESS OTHERWISE SPECIFIED: .X = ± .2 ANGLES ±2° .XX = ± .06 FRACTIONS ±1/32 .XXX= ± .03 REMOVE BURRS AND BREAK EDGES .005 DO NOT SCALE THIS PRINT	DRAWN BY: MSM	SHEET: 1 of 1	PART NUMBER: EQ-P0814-B
	CHECKED BY: TP	SCALE: NTS	DESCRIPTION: 8' X 14' Platform Base
	DATE: 02/18/11	MATERIAL: A36, A568, A572	DRAWING TYPE: ASSEMBLY DRAWING
	REVISION: A	FINISH: GALV A123 WEIGHT: 1742.88 LBS	 ORLAND PARK, IL. 60462 U.S.A.