


# EH1458-002 | LC DUPLEX ADAPTER, W/O FLANGE, AQUA, W/P

---



Fiber Optic Duplex Adapter, Multimode LC/UPC, OM3/OM4, aqua, flangeless

## Product Classification

**Regional Availability** Asia | EMEA | Latin America | North America  
**Product Type** Fiber adapter

## General Specifications

**Body Style** Duplex  
**Color** Aqua  
**Interface** LC/UPC  
**Mounting** No flange  
**Shuttered** No  
**Total Ports, quantity** 2  
**Transmission Standards** IEC 60754-1 | IEC 61300-3-42

## Dimensions

**Width** 15.4 mm | 0.606 in  
**Length** 29.2 mm | 1.15 in

## Material Specifications

**Alignment Sleeve Material** Zirconia

## Optical Specifications

**Fiber Mode** Multimode  
**Insertion Loss, maximum** 0.2 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)  
**Flammability Rating** UL 94 V-0

# EH1458-002 | LC DUPLEX ADAPTER, W/O FLANGE, AQUA, W/P

---

## Packaging and Weights

<b>Included</b>	Dust caps
<b>Packaging Type</b>	Bag

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

