	8	7		6	
ITEM	PART NO.	DESCRIPTION	Q	ΓY.	WEIGHT
1	MTC328401	CHAINMOUNT WELDMEN	IT í	1	9.97 LBS
2	G4096	G-43 CHAIN, 8'		2	6.00 LBS
3	CM.04	1/2" RIGHT HAND THREAD J.	AW 2	2	0.54 LBS
4	GN-04	1/2" GALV HEX NUT		2	0.04 LBS
5	GWL-04	1/2" GALV LOCK WASHE	R 2	2	0.09 LBS
6	GUB-4240	1/2" X 2-1/2" X 4" GALV U-B0	OLT 2	2	0.57 LBS
7	CM.03	CHAIN LOCK		2	0.20 LBS


D

С

В


А

8



5


5



6



7



4	l	3			2		1		
	'		70	1	REVISIONS				]
	-	A REV.	ZONE		DESCRIPTION INITIAL RELEASE		BY DRR	DATE 10/04/11	-
		2			CHCHCHC				D
	 6								C
		1			34	5			В
These drawinas and specifi	cations are the proprietary o	roperty DRAWN BY:	SHEET:						
of CommScope Inc. and purpose authorized in	cations are the proprietary p may be used only for the s n writing by CommScope Inc.	011201120 01.	SCALE:	of 1	PART NUMBER: RR-CM130				-
ALL DIMENSIONS TOLERANCES UNLES	ARE IN INCHES U.O.S. SS OTHERWISE SPECIFIED:	TP	NTS MATERIAL:		SINGLE SECTOR PIPE RIN DRAWING TYPE:	IG MOUNT			4
$X = \pm .12$ .XX = ± .06	ANGLES ±2	/32	11 A36		ASSEMBLY DRAWING				
.XXX= ± .031		REVISION	FINISH: GAL\	/ A123		\\/E	STCHESTER		
	and break edges .005 CALE THIS PRINT	A	weight 25.2	9 LBS	ANDE	REW ® U.S.		, il. 00104	
4		3	I		2		1		L