

# FGS-HTBK-12-5

---



## FiberGuide® 12in Horizontal Tool-less Bracket Kit, 5in Tall, 4x12in

This 12 inch bracket attaches to 12 inch ladder rack using our tool-less Quick Knobs. Used to mount and support 4x12in FiberGuide® above ladder racking.

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

### General Specifications

<b>Color</b>	Black
<b>Note</b>	Includes fastening hardware
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket
<b>Bracket Type</b>	Center Support
<b>Bracket Installation Type</b>	No Brackets
<b>Attachment Type</b>	Ladder rack

### Dimensions

<b>Height</b>	171.374 mm   6.747 in
<b>Width</b>	114.3 mm   4.5 in
<b>Length</b>	306.426 mm   12.064 in
<b>Thread Size</b>	N/A
<b>System Dimensions</b>	102 mm x 305 mm (4 in x 12 in)

### Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

# FGS-HTBK-12-5

---

## Packaging and Weights

<b>Included</b>	Hardware
<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.953 kg   2.1 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

HDW-12021 – FiberGuide® Quick Knob with T-Bolt

# HDW-12021

---



## FiberGuide® Quick Knob with T-Bolt

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber raceway hardware
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS
<b>Minimum Order Quantity</b>	10

### General Specifications

<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Accessory

### Dimensions

<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   102 mm x 305 mm (4 in x 12 in)   102 mm x 610 mm (4 in x 24 in)   51 mm x 152 mm (2 in x 6 in)
--------------------------	--

### Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

### Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.015 kg   0.033 lb

### Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# HDW-12021

---

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

