

# FGS-HTBK-12-5-80PC



FiberGuide® 12in Horizontal Tool-less Bracket Kit for 4x12in System, 5in Tall, kit of 80

This 12 inch bracket attaches to 12 inch ladder rack using our tool-less Quick Knobs. Used to mount and support 4x12in FiberGuide® above ladder racking. Ships in a kit of 80 brackets.

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

## General Specifications

Color	Black
Note	Includes fastening hardware
Orientation	Horizontal
Section Type	Bracket
Bracket Type	Center Support
Bracket Installation Type	N/A
Attachment Type	Ladder rack

## Dimensions

Height	171.374 mm   6.747 in
Width	114.3 mm   4.5 in
Length	306.426 mm   12.064 in
Thread Size	N/A
System Dimensions	102 mm x 305 mm (4 in x 12 in)

## Packaging and Weights

Packaging quantity	80
--------------------	----

# FGS-HTBK-12-5-80PC

---

**Weight, net** 80.168 kg | 176.74 lb

## Included Products

HDW-12021 – FiberGuide® Quick Knob with T-Bolt

# HDW-12021



FiberGuide® Quick Knob with T-Bolt

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber raceway hardware
Product Brand	FiberGuide®
Product Series	FGS
Minimum Order Quantity	10

## General Specifications

Color	Black
Orientation	Horizontal
Section Type	Accessory

## Dimensions

System Dimensions	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   102 mm x 305 mm (4 in x 12 in)   102 mm x 610 mm (4 in x 24 in)   51 mm x 152 mm (2 in x 6 in)
-------------------	--

## Environmental Specifications

Flammability Rating	CSA S143   UL 2024   UL 94 V-0
Halogen Characteristics	Blue Angel   TCO '99   WEEE
Safety Standard	CSA   UL

## Packaging and Weights

Packaging quantity	1
Weight, net	0.015 kg   0.033 lb

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# HDW-12021

---

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

