

# FGS-HTBK-12-5-80PC

---



FiberGuide® 12in Horizontal Tool-less Bracket Kit for 4x12in System, Kit of 80

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber raceway support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Black
<b>Note</b>	Includes fastening hardware
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket

## Dimensions

<b>Height</b>	171.374 mm   6.747 in
<b>Width</b>	114.3 mm   4.5 in
<b>Length</b>	306.426 mm   12.064 in
<b>System Dimensions</b>	102 mm x 305 mm (4 in x 12 in)

## Packaging and Weights

<b>Packaging quantity</b>	80
<b>Weight, net</b>	80.168 kg   176.74 lb

## Included Products

HDW-12021 – FiberGuide® Quick Knob with T-Bolt

# HDW-12021

---



## FiberGuide® Quick Knob with T-Bolt

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber raceway hardware
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Black
--------------	-------

## Dimensions

<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   102 mm x 305 mm (4 in x 12 in)   102 mm x 610 mm (4 in x 24 in)   51 mm x 152 mm (2 in x 6 in)
--------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------

## Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



