



Fiber Optic LGX/1000 Style Multimode OM4 Distribution Module, 8LC to 1x8 MPO, Method A

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module

General Specifications

Functionality	Breakout
Adapter Color	Aqua
Interface, front	LC/UPC + MPO
Polarity	Method A
Total Fibers, quantity	8
Total Ports, quantity, front	9
Total Ports, quantity, rear	0

Dimensions

Height	129.03 mm 5.08 in
Width	28.96 mm 1.14 in
Depth	76.2 mm 3 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum	0.66 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

