



OFDC-A4 Fiber Optic Splice/Patch Closure, gel cable sealing, 12 splices, 4 SC/APC adapters, 1-2 + 1-4 splitter pre-conn at drop side

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and seperate zones for looped cable storage for micro-sheet cables only
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Regional Availability	North America
Product Type	Single-ended, rectangular fiber closure
Product Series	OFDC


General Specifications

Cable Ports Quantity, total	2 round ports + 4 multi-out ports (8 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Manhole Pedestal Strand Wall
Port Type	SC/APC
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink
Splitter Type	1 x 2 1 x 4
Splitter, quantity	2

Dimensions

Height	70 mm 2.756 in
Width	94 mm 3.701 in
Length	211 mm 8.307 in

Ordering Tree



Material Specifications

Material Type

Rugged polymer

Environmental Specifications

Installation temperature

-5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature

-30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity

93%, non-condensing

Environmental Space

Above ground | Below ground

Qualification Standards

IEC 60529, IP68 + 2 m waterhead

UV Resistance

UV stabilized

Packaging and Weights

Packaging quantity

1

Packaging Type

Box | Carton

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

Classification

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

