


FPCA-MMYP



Fiber Optic Patch Cord, singlemode, 1.2 mm OFNP jacket, LC/APC-LC /APC, yellow

- 1.2 mm diameter cable provides a 65% space savings over commonly used 2.0 mm cable
- 1.2 mm diameter fiber patch cords use Reduced Bend Radius (RBR) fiber cable
- Typically used in environments where space constraints and cable routing prove most challenging

Product Classification

Regional Availability	Europe Latin America Middle East/Africa North America
Product Type	Fiber patch cord, simplex
Product Series	FPCA

General Specifications


Connector A, quantity	1
Color, boot A	Green
Color, connector A	Green
Connector B, quantity	1
Color, boot B	Green
Color, connector B	Green
Interface, Connector A	LC/APC
Interface, Connector B	LC/APC
Jacket Color	Yellow
Total Fibers, quantity	1
Transmission Standards	TIA/EIA-604 FOCIS-3

Dimensions

Diameter Over Jacket	1.2 mm 0.047 in
----------------------	-------------------

Ordering Tree

FPCA-MMYP



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2/B2
Insertion Loss, maximum, connector A	0.35 dB
Insertion Loss, maximum, connector B	0.35 dB
Return Loss, minimum, connector A	65 dB
Return Loss, minimum, connector B	65 dB

Environmental Specifications

Environmental Space	Plenum
Qualification Standards	GR-326 CORE GR-409 GR-449-CORE

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

FPCA-MMYP

ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

