

SA-3C



PIM-free, Composite Snap-in Hanger Adapter. Two sets of slots for round member attachment. 3/8 inch holes for bolt down attachment.

Product Classification

Product Type	Adapter
Product Brand	PIM-Guard
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Stand-off adapter
Color	Black
Mounting	3/4 in through hole

Dimensions

Height	36.322 mm 1.43 in
Outside Width	40.132 mm 1.58 in
Outside Length	87.122 mm 3.43 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Maximum Loading	Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411, SSH-1117
Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥1000 hours

Packaging and Weights

SA-3C

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.27 kg 0.595 lb