EG1846-004 | OFDC-B8G-SX2/8-NN-NN-1



OFDC B8G Fiber Optic Splice/Patch Closure, X-press version, Gel Cable sealing, 1 pre-installed 18-fiber splice tray, 1 pre-installed 12 fiber tray, 8 SC/APC adapters,

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and seperate zones for looped cable storage for most cable types
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Regional Availability Australia/New Zealand

Product Type Single-ended, rectangular fiber closure

Product Series OFDC

General Specifications

Cable Ports Quantity, total4 round ports + 8 round ports

Cable Sealing TypeCompressed gelClosure Sealing TypeHinged with latchClosure StyleSingle-ended

Color Black

Mounting Manhole | Pedestal | Strand | Wall

Port Type SC/APC

Splice Tray Included, quantity 2

Splice Tray Type Included 12-way, heat shrink (1) + 18-way, heat shrink (1)

Splitter Type No splitter

Splitter, quantity 0

Dimensions

 Height
 128 mm | 5.039 in

 Width
 156 mm | 6.142 in


 Length
 324 mm | 12.756 in

Page 1 of 3



EG1846-004 | OFDC-B8G-SX2/8-NN-NN-1

Ordering Tree



Material Specifications

Material Type Rugged polymer

Environmental Specifications

Installation temperature $-5 \,^{\circ}\text{C}$ to +45 $^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +113 $^{\circ}\text{F}$)

Storage Temperature $-30 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Relative Humidity 93%, non-condensing

Environmental SpaceAbove ground| Below groundQualification StandardsIEC 60529, IP68 + 2 m waterhead

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 2 of 3



EG1846-004 | OFDC-B8G-SX2/8-NN-NN-1

ROHS UK-ROHS Compliant Compliant





