

F1A-PNFQM

Base Product



FSJ1-50A SureFlex® Jumper with interface types N Female and QMA Male

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	N Female
Specification Sheet Revision Level	A
Variable Length	For custom lengths, contact your local ANDREW representative

Dimensions

Length	0 m 0 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.04

Jumper Assembly Sample Label

F1A-PNFQM



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition