

VIP4302 | VIP4302 Compact IP Set-Top

Base Product



IPTV, OTT, HEVC, HD Compact Set-Top with optional 802.11ac Wi-Fi

- Compact HD Set-top with HEVC decode
- Available in multiple bottom cover colors
- Support for DVR/PVR and Time Shift through ARRIS DVR One stackable USB-connected device
- Optional 802.11ac 2x2 dual band Wi-Fi for high quality IPTV application (VIP4302 W)
- Optional Bluetooth® Low Energy Remote Control (VIP4302 BT)
- Fast Boot

The VIP4302 is an HEVC capable IP set-top box in a stylish design which delivers stunning high definition video viewing experiences. This compact HD client offers DVR and time-shift support through external USB devices. Optional 802.11ac Wi-Fi connectivity ensures high quality IPTV delivery. The ARRIS Fast Boot procedure is implemented on this model.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	IP video device

General Specifications

Graphics	OpenGL 2.0, 1 Gpix/s
Hard Disk	Supports DVR-One stackable disk unit
Memory	1 GB DDR3 256 MB Flash
Network Interface	Ethernet Wi-Fi
Processor	6000 DMIPS
Remote Interfaces	Bluetooth Low Energy (optional) IR
Software Compatibility	ARRIS KreaTV
Tuner	IP
Video Formats	HD
Video Resolution	1080i 1080p60 720p
Wi-Fi Interface Standard	2x2 IEEE 802.11ac (optional)

Dimensions

Height	25.908 mm 1.02 in
Diameter	130.048 mm 5.12 in

Logo Image



Environmental Specifications

- Operating Temperature** 0 °C to +40 °C (+32 °F to +104 °F)
- Relative Humidity** 8%–95%
- Standards Compliance** CE | IVA | PCoC | RoHS Compliant | WEEE

Packaging and Weights

- Weight, net** 0.209 kg | 0.46 lb