## 760043000 | IR12SP

### IR12SP 2-port Single Gang Stainless Steel Industrial Faceplate

#### Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFaceplate kitProduct SeriesM Series

## General Specifications

ANSI/TIA Category 5e | 6 | 6A

**Application** Used with M Series modular information outlet

ColorSilverMountingFlushTotal Ports, quantity2

#### **Dimensions**

 Height
 114.3 mm | 4.5 in

 Width
 69.85 mm | 2.75 in

 Receptacle Opening
 27.94 mm | 1.1 in

## Material Specifications

Material Type Stainless steel

## **Environmental Specifications**

**Operating Temperature**  $-25 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \left(-13 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F}\right)$ 

Flammability Rating UL 94 V-0

**Qualification Standards** IEC 60529: 2001, IP44

Safety Standard UL | cUL

## Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications



# 760043000 | IR12SP

Agency	Classification
--------	----------------

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

