



2 Port Industrial Box

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Surface mount box

General Specifications

ANSI/TIA Category	5e 6 6A
Application	Provides sealed copper connectivity
Color	Gray
Mounting	Surface
Total Ports, quantity	1

Dimensions

Height	119.38 mm 4.7 in
Width	78.74 mm 3.1 in
Depth	82.55 mm 3.25 in
Plug Diameter	29.21 mm 1.15 in
Receptacle Opening	27.94 mm 1.1 in

Material Specifications

Material Type	Aluminum
----------------------	----------

Environmental Specifications

Operating Temperature	-25 °C to +85 °C (-13 °F to +185 °F)
Flammability Rating	UL 94 V-0

760080820 | MIB-2

Qualification Standards IEC 60529, IP65

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Weight, net 0.544 kg | 1.2 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

