

760154096 | H61A-226-GREEN

High Density Icon Strip, green, bulk pack



OBSOLETE

Replaced By:

760164400 HGS620 Icon Strip (Voice / Data / Blank), Green (25 ea/pkg)
H61K-ICON-GN

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Icon kit
Ordering Note	Minimum order quantity, 20 packs

General Specifications

Color	Green
-------	-------

Dimensions

Height	13.97 mm 0.55 in
Width	23.62 mm 0.93 in
Depth	2.79 mm 0.11 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	25
--------------------	----

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

