760181768 | M28L-266

M28L-266 Faceplate, pro white

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFaceplate kitProduct SeriesM Series

General Specifications

Application Used with M Series modular information outlet

ColorPro whiteMountingFlushTotal Ports, quantity8

Dimensions

 Height
 117.094 mm | 4.61 in

 Width
 122.174 mm | 4.81 in

 Depth
 7.366 mm | 0.29 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Weight, net 0.054 kg | 0.12 lb

Regulatory Compliance/Certifications

Agency Classification



760181768 | M28L-266

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

