2269081-2

High-Density Front-Loading Cable Manager Shallow, 2U

- Offers bend radius and mechanical protection
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords
- Suitable for Twisted Pair and Fiber Optic patch cords

Product Classification

Regional Availability	Asia	Australia/New Zealand	EMEA	Latin America	North America
Portfolio	CommScope®
Product Type	Cable management hardware
Minimum Order Quantity	8
Ordering Note	Sold per piece with an MOQ of 8 pieces

General Specifications

Color	Black
Rack Units	2

Dimensions

Height	88.9 mm	3.5 in
Width	63.5 mm	2.5 in
Depth	98.044 mm	3.86 in

Material Specifications

Finish	Smooth
Material Type	Galvanized steel	PA	TPE

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL	cUL

Packaging and Weights

Packaging quantity	1

COMMSCOPE®

2269081-2

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

COMMSCOPE®