

RJ45 Modular Plug Kit, category 5E, shielded, 8-position

OBSOLETE
Replaced By:

6-2111988-2
MP-5EMT-C-5

Modular Plug, category 5e, shielded, cable diameter 5.7–7.0 mm, 500 pcs

6-2111988-3
MP-5EMT-C-1

Modular Plug, category 5e, shielded, cable diameter 5.7–7.0 mm, 100 pcs

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	5e
Cable Type	Round, shielded
Conductor Type	Stranded
Interface	RJ45
Positions/Loaded Contacts	8/8
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	7 mm 0.276 in
Compatible Cable Diameter, minimum	6 mm 0.236 in

Electrical Specifications

Insulation Resistance, minimum	500 mOhm
--------------------------------	----------

Material Specifications

Contact Base Material	Phosphor Bronze
Material Type	Glass filled polycarbonate
Plug Shield Base Material	Brass

336462-1

Plug Shield Plating Material Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Flammability Rating UL 94 V-2

Packaging and Weights

Packaging quantity 1000

Packaging Type Bag | Box | Carton