

5-1479185-1



Modular Plug, category 6, unshielded, 8-position, round cable, 1000 pcs

OBSOLETE

This product was discontinued on: August 14, 2018

Replaced By:

6-2111989-2
MP-6S-C-5

Modular Plug Kit, category 6, shielded, 8-position, 5.7 – 7.0 mm max cable jack OD, 500/bag

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	6
Cable Type	Round, unshielded
Conductor Type	Solid
Interface	RJ45
Positions/Loaded Contacts	8/8
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	7 mm 0.276 in
Compatible Cable Diameter, minimum	6 mm 0.236 in
Compatible Insulated Conductor Diameter, maximum	1 mm 0.039 in
Compatible Insulated Conductor Diameter, minimum	0.89 mm 0.035 in

5-1479185-1

Compatible Conductor Gauge, solid

24–23 AWG

Electrical Specifications

Insulation Resistance, minimum

500 m0hm

Material Specifications

Contact Base Material

Phosphor Bronze

Material Type

Glass filled polycarbonate

Plug Shield Base Material

Brass

Plug Shield Plating Material

Nickel

Mechanical Specifications

Plug Insertion Life, minimum

750 times

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Flammability Rating

UL 94 V-2

Packaging and Weights

Packaging quantity

1000

Packaging Type

Bag | Box | Carton