

Modular Plug, category 6, shielded, 8-position, round cable, 100 pcs

OBSOLETE
This product was discontinued on: August 14, 2018
Replaced By:
6-2111981-3
MP-6AS-B-1

Modular Plug Kit, category 6A, shielded, 8-position, 5.1 – 6.0 mm max cable jack OD, 100/bag

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	6
Cable Type	Round, shielded
Conductor Type	Stranded
Interface	RJ45
Positions/Loaded Contacts	8/8
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	6 mm 0.236 in
Compatible Cable Diameter, minimum	5.3 mm 0.209 in

Electrical Specifications

Insulation Resistance, minimum	500 mOhm
--------------------------------	----------

Material Specifications

Contact Base Material	Phosphor Bronze
Material Type	Glass filled polycarbonate
Plug Shield Base Material	Brass
Plug Shield Plating Material	Nickel

5-1711345-3

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 100

Packaging Type Bag | Box | Carton