

5-557971-2

Modular Plug, 6P/6C, unshielded, flat oval, small conductor, 6-position, category 3, 500 pcs

OBSOLETE

This product was discontinued on: August 14, 2018

Replaced By:

6-557971-2
MP-66U-FS-5

Modular Plug, 6P/6C, unshielded, small conductor, std. body, flat oval, 2.29x6.61 mm cable jack OD, 500/bag

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	3
Cable Type	Flat oval, unshielded
Conductor Type	Solid
Interface	RJ12
Positions/Loaded Contacts	6/6
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	4.01 mm 0.158 in
Compatible Insulated Conductor Diameter, maximum	0.86 mm 0.034 in
Compatible Insulated Conductor Diameter, minimum	0.74 mm 0.029 in
Compatible Conductor Gauge, solid	28–26 AWG

Electrical Specifications

Current Rating, maximum	0.75 A
Insulation Resistance, minimum	500 mOhm
Safety Voltage Rating	150 Vac

Material Specifications

5-557971-2

Contact Base Material	Phosphor Bronze
Material Type	Glass filled polycarbonate
Mechanical Specifications	
Plug Insertion Life, minimum	750 times
Environmental Specifications	
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing
Flammability Rating	UL 94 V-2
Packaging and Weights	
Packaging quantity	500
Packaging Type	Bag Box Carton